



REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C3	ECR-22-148170	07MAY2024	BP	CW

NOTES:

- ELECTRICAL DATA: CONTACT RESISTANCE: 10 mOhm MAX
INSULATION RESISTANCE: 100 MOhm MIN at 500VDC
CURRENT RATING: 5 AMPS
BREAKDOWN VOLTAGE: 500 VAC MIN PER MINUTE
- ENVIRONMENTAL: OPERATING TEMPERATURE: -20°C TO +80°C
SEALING REQUIREMENTS: IP67
- PROD SPEC: 108-3641
- PACKAGING: 107-3334
- FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED

ITEM	DESCRIPTION	MATERIAL	FINISH/COLOUR	QTY
1	SCREW NUT	ZINC DIE CAST	2.5µm NICKEL PLATED	1
2	CONNECTOR BODY	POLYURETHANE	BLACK	1
3	SOCKET CONTACT	BRASS	0.15µm GOLD OVER NICKEL	3
4	3 CORE CABLE (CORES 22AWG TO UL2464)	PVC JACKET UV RESISTANT	BLACK	1
5	'O' RING	VITON	GREEN	1



OBSOLETE

OBSOLETE	10000	500 mm	M8 RIGHT ANGLED FEMALE CONNECTOR 10.0m CABLE	1838296-5
OBSOLETE	7000	350 mm	M8 RIGHT ANGLED FEMALE CONNECTOR 7.0m CABLE	1838296-4
OBSOLETE	5000	250 mm	M8 RIGHT ANGLED FEMALE CONNECTOR 5.0m CABLE	1838296-3
OBSOLETE	3000	150 mm	M8 RIGHT ANGLED FEMALE CONNECTOR 3.0m CABLE	1838296-2
OBSOLETE	2000	100 mm	M8 RIGHT ANGLED FEMALE CONNECTOR 2.0m CABLE	1838296-1
	DIM A	TOL 'B'	DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	DWN MANJUNATH.T.N 29MAR06	STE TE Connectivity	
		CHK F.WHEELER-KING 07AUG06		
MATERIAL	FINISH	APVD F.WHEELER-KING 07AUG06	NAME M8 RIGHT ANGLED FEMALE CONNECTOR WITH STRAIN RELIEF 3 POSITION, PVC CABLE	RESTRICTED TO
		PRODUCT SPEC	SIZE A3	CAGE CODE 00779
		APPLICATION SPEC	DRAWING NO C-1838296	SCALE NTS
		WEIGHT 0.000000		SHEET 1 OF 1
		CUSTOMER DRAWING		REV C3