

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

REVISIONS

© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	29MAY2019	OL	SZ
	A1	REVISED -2	02MAR2023	CZ	SH

1.00
3.85
1.02
14.0 REF.

0.70
(EXCEPT -1 / -2)
1
6.85

NOTES:

1. PART NUMBER AND DATE CODE.

2. MATERIAL: THERMO PLASTIC, UL94 V-0, COLOR: SEE PART NUMBER LIST.

3. THIS RECEPTACLE HOUSING TO BE USED WITH RECEPTACLE TERMINAL 2204749.

4. PACKAGED IN BULK BY BAG.

1.65
1.95
5.40
3.00
6.85
3.00 (PITCH)
DIM.A
DIM.B
DIM.C
PIN 2#
PIN 1#
LAST PIN

36.85	35.40	33.00	NATURE	24	2-2204748-4
33.85	32.40	30.00	NATURE	22	2-2204748-3
30.85	29.40	27.00	NATURE	20	2-2204748-2
27.85	26.40	24.00	NATURE	18	2-2204748-1
24.85	23.40	21.00	NATURE	16	2-2204748-0
21.85	20.40	18.00	NATURE	14	1-2204748-9
18.85	17.40	15.00	NATURE	12	1-2204748-8
15.85	14.40	12.00	NATURE	10	1-2204748-7
12.85	11.40	9.00	NATURE	8	1-2204748-6
9.85	8.40	6.00	NATURE	6	1-2204748-5
6.85	5.40	3.00	NATURE	4	1-2204748-4
3.85	2.40	N/A	NATURE	2	1-2204748-3
DIM.C	DIM.B	DIM.A	COLOR	CIRCUIT	PART NUMBER

36.85	35.40	33.00	BLACK	24	1-2204748-2
33.85	32.40	30.00	BLACK	22	1-2204748-1
30.85	29.40	27.00	BLACK	20	1-2204748-0
27.85	26.40	24.00	BLACK	18	2204748-9
24.85	23.40	21.00	BLACK	16	2204748-8
21.85	20.40	18.00	BLACK	14	2204748-7
18.85	17.40	15.00	BLACK	12	2204748-6
15.85	14.40	12.00	BLACK	10	2204748-5
12.85	11.40	9.00	BLACK	8	2204748-4
9.85	8.40	6.00	BLACK	6	2204748-3
6.85	5.40	3.00	BLACK	4	2204748-2
3.85	2.40	N/A	BLACK	2	2204748-1
DIM.C	DIM.B	DIM.A	COLOR	CIRCUIT	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 9-Aug-18

CHK RADAR SUN 9-Aug-18

APVD SUNY ZHAO 9-Aug-18

SUNY ZHAO

PRODUCT SPEC

108-128068

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

TE Connectivity

NAME ELCON MICRO POWER CONNECTOR, RECEPTACLE, HOUSING, 3.00MM PITCH, 2XN CIRCUITS

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2204748	-

SCALE	SHEET	OF	REV
4:1	1	2	A1

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0.30
2 PLC	±0.20
3 PLC	±
4 PLC	±
ANGLES	±
FINISH	-

MATERIAL

-

-

1470-19 (3/13)

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


20

© COPYRIGHT 20 BY -


ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




CIRCUIT SIZE:2




CIRCUIT SIZE:8




CIRCUIT SIZE:14




CIRCUIT SIZE:20




CIRCUIT SIZE:4




CIRCUIT SIZE:10




CIRCUIT SIZE:16




CIRCUIT SIZE:22




CIRCUIT SIZE:6



CIRCUIT SIZE:12



CIRCUIT SIZE:18




CIRCUIT SIZE:24

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±-
- 1 PLC ±±0.30
- 2 PLC ±±0.20
- 3 PLC ±-
- 4 PLC ±-
- ANGLES ±-
- FINISH -

MATERIAL

-

DWN 9-Aug-18

RADAR SUN

CHK 9-Aug-18

SUNY ZHAO

APVD 9-Aug-18

SUNY ZHAO

PRODUCT SPEC 108-128068

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME ELCON MICRO POWER CONNECTOR, RECEPTACLE, HOUSING, 3.00MM PITCH, 2XN CIRCUITS

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A300779 C-2204748

SCALE 3:1 SHEET 2 OF 2 REV A1