



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	RELEASED PER ECO-20-014572	DF	MM	-
	A1	ECN-22-168414	05AUG2022	CG	JM

MT FERRULE KIT
(COMPONENTS PACKAGED UNASSEMBLED)
2332756-1 SHOWN



- 1 MATERIAL= MT FERRULE: THERMOPLASTIC PER ASTM D4067
FERRULE COVER: ABS PER ASTM D4673
MINI BOOT: VULCANIZED THERMOPLASTIC POLYOLEFIN
SPRING: 300 SERIES, STAINLESS STEEL WIRE, PER ASTM A313
PIN HOLDER: 300 SERIES, STAINLESS STEEL, PER ASTM A617
PINS: 400 SERIES, STAINLESS STEEL, PER ASTM A276
- 2 FINISH= SPRING: PASSIVATED
- 3 WEIGHT CALCULATIONS FOR REFERENCE ONLY.

0.560	RECEPTACLE, VITA 66.5 STYLE A 2332700-1	24 FIBER, MULTI-MODE, LOW-LOSS GRADE	2332756-2
0.562	RECEPTACLE, VITA 66.5 STYLE A 2332700-1	12 FIBER, MULTI-MODE, LOW-LOSS GRADE	2332756-1
KIT WEIGHT (GRAMS) 3	USED WITH	MT FERRULE TYPE	KIT PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. FABIAN 31JULY2018	 TE Connectivity	
DIMENSIONS:		CHK J. MOSIER 31JULY2018		
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MT FERRULE KIT, WITH PINS MM, 50/125 LOW-LOSS GRADE FOR VITA 66.5 RECEPTACLE CONNECTORS
APVD J. MOSIER 31JULY2018				
PRODUCT SPEC				
APPLICATION SPEC				
- -<				