

Interface Dimension <u>1.0mm male and</u>	TEMPERATURE RANGE -55 ℃~+125 ℃
	ROHS COMPLIANT
Force to Engage and Disengage Engage: N/A Disengage: N/A Center Cantact Captivation Axial (N) 26.0 MIN Radial (In/Oz) N/A Cable Retention Axial (Lbs) N/A Mating cycles 500_cycles	
	1.35mm female Force to Engage and Disengage Engage: N/A Disengage: N/A Center Cantact Captivation Axial (N) 26.0 MIN Radial (In/Oz) N/A Cable Retention Axial (Lbs) N/A

В

1	SHELL	S	TAINLESS STEEL	PASSIVATION	I
1	CONTACT PIN B		YLLIUM COPPER	GOLD 20-50 u"/ NICKEL 30 u"	
1	INSULATOR		PEEK	N/A	
1	BODY	S	AINLESS STEEL	PASSIVATION	
2385345-1	PART NUMBER		MATERIAL	PLATING	
	ONTROLLED DOCUMENT. DWN PENG CHK ROGF	28JAN2021 ZHAI 28JAN2021 SONG	TE	TE Connectivity	
	TOLERANCES UNLESS OTHERWISE SPECIFIED: INOGL APVD 0 PLC + - 1 PLC ± 0.3 .2 PLC ± 0.2 3 PLC ± 0.1	28JAN2021 E HE PEC		le to 1.35mm Female Adapter —	
MATERIAL	4 PLC ± - ANGLES ± 5° — FINISH WEIGHT	_	SIZE CAGE CODE DRAWING NO $A200779$ C=238	85345	RESTRICTED TO
_	CUSTO	MER DRAWING	• • •	SCALE 1:1 SHEET 1 OF	1 REV A

А

g 2385345