



TECHNICAL DATA

MATERIAL

Housing: Thermoplast PA6 GF25

MECHANICAL DATA

Protection: Interior IP40 DIN 40050
Connections IP 00 DIN 40050
Temperatur Range: -40° to +70°C

ELECTRICAL DATA

Voltage Range: 18 - 32 VDC
Pull In Current: 1000 A at 24 VDC
Duty Rating: 500 A at 24 VDC
Electrical Life: 10 000 Cycles

	Date	Name	mm	Scale		Drawing No:
Drawn	06.11.2000	Walz	↔	1:2		24-01-00-901
Check	06.03.2017	Lugin	General Tolerances DIN ISO 2768 cL		NSN:	