



PCB Layout

REVISONS		DATE	OWN	APP'D
P	LTN			
A	FIRST VERSION	23NOV2015	C.F	S.M

LOC	POST	DESCRIPTION	DATE	OWN	APP'D

  

④	③	②	①
SPRING	COVER	CONTACT	HOUSING
8 POSN	7 POSN	6 POSN	5 POSN
2834099-7	2834099-6	2834099-5	2834099-4
			2834099-3
			2834099-2
			2834099-1

COLOR	DIM A	NO. OF POSITIONS	PART NO
GRAY	43.54	8 POSN	2834099-7
	38.46	7 POSN	2834099-6
	33.38	6 POSN	2834099-5
	28.30	5 POSN	2834099-4
	23.22	4 POSN	2834099-3
	18.14	3 POSN	2834099-2
	13.06	2 POSN	2834099-1

- NOTES :
- △ MATERIALS AND FINISH:
    - HOUSING: PA66
    - CONTACTS: BRASS, FINISH: TIN OVER NICKEL UNDERPLATE
  - 2. MUST COMPLY WITH DIRECTIVE 2002/95/EC (RoHS)
  - 3. WIRE TYPES AND SIZES ACCEPTED
  - WIRE RANGE: 12AWG~28AWG.
  - STRIP LENGTH: 5~6mm
  - 4. PACKAGED IN TRAY.
  - 5. CURRENT RATING: 20Amp AC300V.
  - 6. OPERATION TEMPERATURE: -40°C TO +105°C
  - 7. THIS PART NO. IS THE SAME STRUCTURE AS THE SERIES: 2834099
  - THE DATASHEET AND MORE DETAILS PLEASE FOLLOW THE SERIES: 2834099

THIS DRAWING IS A CONTROLLED DOCUMENT.

REVISIONS	DATE	OWN	APP'D
LTN			
FIRST VERSION	23NOV2015	C.F	S.M

  

THIS DRAWING IS THE PROPERTY OF STTE. ALL RIGHTS RESERVED.	30
--	----

  

STTE	TE Connectivity
------	-----------------

  

5.08mm Horizontal Entry Screwless Connector	2834099
---	---------