


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - 00779 ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A	NEW RELEASE	13JUN2018	GK KM



LABEL ACROSS: 2
LABELS PER SHEET: 10
LABELS PER PACK: 100
SHEETS PER PACK: 10
 All dimensions in INCHES[mm]

TE PN: 572792-000

MATERIAL	PE200-LASER PRINTABLE POLYESTER, MATTE SILVER
ADHESIVE TYPE	ACRYLIC PERMANENT
LINER	WHITE KRAFT
PRINT	BLACK COLOUR

TOLERANCES INCH [mm]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 13JUN2018 GOPALAKRISHNA HV	
LABEL HEIGHT:	±.012 [0.3]	DIMENSIONS: INCHES [mm]		CHK 13JUN2018 K. MUNZ	
LABEL WIDTH:	±.012 [0.3]			APVD 13JUN2018 K. MUNZ	
WEB WIDTH:	±.031 [0.8]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ± FINISH -		NAME LM - METALLIZED POLYESTER LABELS ON SHEET	
VERTICAL REPEAT:	±.031 [0.8]*			PRODUCT SPEC TIDS-070	
HORIZONTAL REPEAT:	±.031 [0.8]*			APPLICATION SPEC	
PRINT POSITIONING:	±.031 [0.8]*			SIZE CAGE CODE DRAWING NO RESTRICTED TO A2 C2290 C=319-LM	
LEFT MARGIN:	±.016 [0.4]	MATERIAL SEE TABLE		WEIGHT 1.60 g	
QUANTITY:	-0 % +2 % *NON ACCUMULATING			CUSTOMER DRAWING	