






Für diese Zeichnung behalten wir uns das Urheberrecht gemäß DIN 34 vor



Technical Data:

Case Material: Cover	Vyncolit black
Base Plate	PA GF black
Key Plate	PA GF red
Switch Lever Material	PA GF red
Min. Insulation Resistance	100MOhm
Dielectric Withstanding Voltage	1050V-1min
Max. Contact Voltage Drop	150mV
Voltage	up to 32VDC
Continuous Rating	500A
Overload.....	1500A 4min
	2000A 1min
	2500A-10sec
Sealing	IP 67/ IEC 529
Vibration	10G/ 18-500Hz
Weight	340g/ 0.75 Pound
Temperature Range	-40°C to +85°C
Wire Selection (At Nominal Load)	min. 250mm2
Key	not removeable
.....	lockable in "OFF" position
.....	not lockable in "ON" position
Max. Torque (Main Contacts).....	18-22Nm

	Datum	Name	Freimaßtoleranz	Maßstab		Zeichnungs-Nr.:
Bearb.	14.09.2007	Hamar	DIN ISO 2768 mK	1:2		35-514-231-R-900
Gepr.	06.03.2013	Grind				Vers.Nr.: