


350037



1. FOR ADDITIONAL INFORMATION SEE DWG 350019.
 2. THIS TERMINAL TO BE SUPPLIED IN INDIVIDUAL FORM, NOT AS CONTINUOUS STRIP.
- △ 3 PLATED INSIDE WITH .000030 GOLD, OVER .000050 NICKEL UNDERPLATE

PART NO.	MATERIAL & FINISH
350037-1	.008 PH BRZ - PRE-TIN
350037-2	.008 PH BRZ △

G	OBSOLETE PER ECR-22-159524	25NOV22	M.J	T.S	H	REACTIVATE PER ECR-22-161356	15DEC22	M.J	T.S
F	OBSOLETE -6	EM 473	16M/2	8-7-66	© 1971 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENT PENDING. CUSTOMER COPY REFERENCE ONLY				
E1	RESTORED		BD/R	10/1/66					
E	REVISED PER M-	7348	T/M	5/2/63	MATERIAL AND FINISH SEE TABLE				
D	REVISED M-4136		H	3-1-71					
G	REVISED M-4049		H	10-27-71	AMP INCORPORATED HARTFORD, CONN.				
B	ADD'D DIM 6	771	H	1/27/71					
A	REVISED DESIGN	1468	H	4/4/73	WIRE - GAUGE - INSULATION TYPE #26 - #18 .050 - .115 TOLERANCE EXCEPT AS NOTED ± .010 ± 1° 9-1				
LTR	REVISION RECORD	ECN	DATE	DATE					
DR	JIM KUNKLE	DE			NAME .058 DIA RECEPTACLE (LOOSE-PIECE)				
CNR		APP							