



REVISIONS			
Rév.	Description	Visa	Date
A	Drawing creation	EL	30.12.21

Kit size: 86,0 x 210,0
[3.39" x 8.27"]



Recto

Verso




-  x 60 - Black
-  x 60 - Black
-  x 60 - Black
-  x 60 - Blue
-  x 60 - Yellow + Green








TOTAL : 300 labels

50 labels/sheet

6 sheets/kit

TE PN: 2404100-1




-  Kiss cut
-  Die cut
-  Back slit
-  Adhesive cut
-  Perforation
-  45° die cut
-  2 kiss cut enductions

All dimensions in mm/[inch]
Labels are centered on the liner except against indication

Overlamination: /	
Material :	White PVC
Adhesive :	Permanent
Liner:	Kraft
DWN EL / 30.12.21	DATE
CHK EL / 30.12.21	DATE
APVD XX / xx.xx.xx	DATE
PRODUCT SPEC TTDS-280	DATE
APPLICATION SPEC	DATE
WEIGHT 4,2 g (label)	SIZE
SCALE NTS	CAGE CODE
TE Connectivity	
Part	
3PHASES-LABEL-BK-300	
TE DRAWING	RESTRICTED TO
A4	FB1U7
3PHASES-LABEL-BK-300_20211230	
CUSTOMER DRAWING	SHEET 1 OF 1
	REV A

Customer drawing

TOLERANCES	
Label height :	±0,2
Label width :	±0,2
Web width :	±0,5
Vertical repeat :	±0,3*
Horizontal repeat :	±0,5*
Print positioning :	±0,5*
Left margin :	±0,5
Quantity :	0% +2%
* non accumulating	

THIS DRAWING IS A CONTROLLED DOCUMENT	
DIMENSIONS	TOLERANCES UNLESS OTHERWISE SPECIFIED
	0/PLC 1/PLC 2/PLC 3/PLC 4/PLC ANGLES
MATERIAL	FINISH
SEE TABLE	Gloss