


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION ,19 .  
 © COPYRIGHT 19 BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
DF	SO				
	E	REV PER 0H14-0659-04	10-13-04	CT	DE



#22 AWG SILICONE COVERED WIRE  
 COLOR: SEE TABLE

SILICONE RUBBER  
 PER ZZ-R-765

CONTACT PIN  
 MAT'L: BRONZE PER ASTM-B-140  
 FINISH: GOLD PLATED PER MIL-G-45204  
 OVER NICKEL PER QQ-N-290

WHITE	40.00 [1016.0]	867824-4
WHITE	6.00 [152.4]	867824-3
GREEN	24.00 [609.6]	867824-2
WHITE	24.00 [609.6]	867824-1
WIRE COLOR	DIM A	PART NO.

1. MARKED PER MIL-STD-130.
2. THIS PRODUCT IS RATED TO 125°C.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.C. THOMAS 4-22-96	<b>AMP</b> AMP Incorporated Harrisburg, PA 17105-3608												
DIMENSIONS: INCHES [mm]		CHK D.EABY 4-23-96													
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.EABY 4-23-96	NAME RECPT, MICRO-MIN, SINGLE LINE, LGH												
<table border="1"> <tr><td>0 PLC</td><td>±-</td></tr> <tr><td>1 PLC</td><td>±-</td></tr> <tr><td>2 PLC</td><td>±.03 [0.8]</td></tr> <tr><td>3 PLC</td><td>±.015 [0.38]</td></tr> <tr><td>4 PLC</td><td>±-</td></tr> <tr><td>ANGLES</td><td>±-</td></tr> </table>		0 PLC	±-	1 PLC	±-	2 PLC	±.03 [0.8]	3 PLC	±.015 [0.38]	4 PLC	±-	ANGLES	±-	PRODUCT SPEC -	SIZE A3
0 PLC	±-														
1 PLC	±-														
2 PLC	±.03 [0.8]														
3 PLC	±.015 [0.38]														
4 PLC	±-														
ANGLES	±-														
MATERIAL -	FINISH -	APPLICATION SPEC -	CAGE CODE 00779												
		WEIGHT -	DRAWING NO C-867824												
		CUSTOMER DRAWING	SCALE 8:1												
			SHEET 1 OF 1												
			REV E												