

THIS DRAWING IS UNPUBLISHED. VERTRAULICHE UNVEROEFFENTLICHTE ZEICHNUNG.
 BY AMP INCORPORATED. ALL RIGHTS RESERVED. ALLE RECHTE VORBEHALTEN.
 COPYRIGHT 19-



MATED WITH: PASSEND ZU:	LOC AI	DIST -	REVISIONS AENDERUNGEN DESCRIPTION BESCHREIBUNG				DATE	DWN	APVD
-	-	-	P	LTR					
PROJEKT NR.: -				B2	CREATED NEW DRAWING	13-NOV-01	M. T.	M. T.	
				-	-	-	-	-	

Customer Drawing

for PN 927824

SEE 1355048

-	-	-	-	-	-	-	-
CUSTOMER PART NO	AMP PART NO	REV.	PCS.	MATERIAL	SURFACE COLOR	DESCRIPTION	

DIMENSIONS: DIMENSIONEN: mm	DWN	T. Bensch	27-MAY-98	MATERIAL	-	FINISH OBERFLAECHE/FARBE	-
	CHK	V. Huhn	18-MAY-00	 AMP Deutschland GmbH D - 63225 Langen	STANDARD-POWER-TIMER CONTACT STANDARD-POWER-TIMER KONTAKT		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 n. ISO 2768 - mH -E n. DIN 16901 - 140	APVD	M. Bleicher	19-MAY-00				
n. ± n. ± n. ± n. ± n. ± ANGLES/WINKEL ±	PRODUCT SPEC PRODUKTSPEZ.	-	NAME	STANDARD-POWER-TIMER CONTACT STANDARD-POWER-TIMER KONTAKT			
	APPLICATION SPEC VERARBEITUNGSSPEZ.	-	SIZE	CAGE CODE	DRAWING NO ZEICHNUNGS-NR.	RESTRICTED TO NUR FUER	
	WEIGHT GEWICHT	-	A4	00779	C- 927824	-	
CUSTOMER DRAWING				/KUNDENZEICHNUNG		MASSSTAB	BLATT
						1	OF VON 1
						B2	