



NOTE:  
 \* FOR CRIMP DIMENSION INFORMATIONS CONTACT TE CONNECTIVITY ENGINEERING

963894-1	>2.5-4.0mm²	PLAIN [Sn] 1.0-3.0µm	X12 CrNi18-8 CuSn4	STEEL SPRING BODY	2 1
TE PN	WIRE SIZE	FINISH	MATERIAL	COMPONENT	ITEM NO

THIS DRAWING IS A CONTROLLED DOCUMENT. CE SCHEMA EST UN DOCUMENT CONTROLÉ		DMN/DESSINE SHREESHAIL 08AUG2012	TE Connectivity	
DIMENSIONS: mm		CHK/VERIFIE R. KONRAD 08AUG2012	NAME TITRE 6.3mm Receptacle Contact	
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES (SUIV NB DE DECIMALES) 0 PLC / DEC ± 1 PLC / DEC ± 0.2 2 PLC / DEC ± 3 PLC / DEC ± 4 PLC / DEC ± ± 2°		APVO/APPROVE G. MUMPER 08AUG2012	APPLICATION SPEC SPEL APPLICATION	
MATERIAL MATERIE SEE TABLE		FINISH FINITION SEE TABLE	WEIGHT MASSE APPROX	RESTRICTED TO RESERVE A
CUSTOMER DRAWING/PLAN CLIENT		UNIFORMENT POUR REFERENCE	SCALE ECHELLE 10:1	SHEET FEUILLE 1 DE 1