

# 623 Receptacle angled rotatable

speedtec

12-pin insulation insert Code 0° housing code 1 flange mount /Flange 25x25

## A ED C 110 NN 00 00 1115 000 A G C 110 N 00 00 1115 000



**Contact Arrangement** mating view




© 2018 TE Connectivity

TE Connectivity, TE connectivity (logo), intercontec (logo) and speedtec are trademarks.


While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this presentation, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this article are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

TE Connectivity Industrial GmbH Bernrieder Straße 15 94559 Niederwinkling, Deutschland Tel.: +49 9962 2002-0 Fax: +49 9962 2002-70 E-Mail: intercontec@te.com Web: www.intercontec.biz





#### Montagefenster



Main Dimensions Receptacle angled rotatable

\*for max. wire cross-section pay attention to the cross-section of used contacts

temperature range protection type rotation range **Electrical Data** 

**Technical Data** 

number of pins

rated current rated voltage rated insulation voltage (L-L)

mating cycles

seals

#### 500

2000 m

3 ĪII

2500 V

12

3309

signal max. 7 A\* 160 V (AC/DC)

-20 °C to 130 °C when connected IP 66/67

### Data according to VDE 0110/EN61984, Paragraph 6.19.2.2

pollution degree over voltage category max. height for operation

Material housing insulation insert

zinc diecast / chromated PBT, UL 94 / V0 FKM

Contacts (not part of product contents)

Tools (not part of product contents)