



ALL-PURPOSE MOUNT KIT

Die-Cast Enclosure Antennas

ALL-PURPOSE MOUNT KIT

The All-Purpose Mount is an articulation mount that may be used with various models. This mount kit is specifically designed to provide a wide range of articulation and flexibility in both the azimuth and elevation planes. The mount may be used on any vertical wall or mast up to 2 inches in diameter, depending on the model. For best results, mount the antenna near the center of the coverage area. A line-of-sight path between the antenna and active floor locations generally works best. Although 2.4GHz signals penetrate cubical dividers and interior walls with little attenuation, reinforced block walls, banks of metal cabinets or steel shelving may attenuate signals or cause multipath conditions where reflected signals interfere with the primary signal path.

FEATURES



- Allows the antenna to articulate, resulting in better coverage pattern
- Can be mounted on any vertical wall or mast up to 2 inches in diameter, depending on the model

MARKETS

- Available for all the DirectLink series antennas
- Pole, wall and ceiling mounts are also available

PART NUMBER	DESCRIPTION
ALLPMTP	All-purpose mount
ALLPMTA	All-purpose wall mount
ALLPMTB	All-purpose mount for 8 x 13-inch antenna
ALLPMTC	All-purpose mount for 45 x 6.5-inch antenna
ALLPMTD	All-purpose mount for SR240790P antenna
ALLPMTE-001	Universal mast mount bracket for DirectLink series antennas
ALLPMTE-002	Universal mast mount bracket for DirectLink series antennas
TM905BRK	Tilt mount for SR2411120D and S2401290P
BPXCHK	Ceiling mount hardware kit for the BPX-series antenna
BPXPHK	Pole mount hardware kit for the BPX-series antennas

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original