



ULTRALINK COMMERCIAL GRADE CABLE

TL-092463 TL-092887

HIGH EFFICIENCY COMMERCIAL GRADE CABLE

Laird UltraLink mobile cable is constructed with a solid center conductor for the secure attachment of crimp-on connectors. Laird Ultralink cable is insulated with a layer of low loss Teflon® dielectric which withstands the high temperatures encountered in mobile applications.

In addition Laird applies a layer of easily removed friction bound aluminum foil for 100% shielding and tinned copper braid with full 95% coverage ensuring good grip to the connector's outer shell. The Laird Ultralink cable is jacketed in a smooth, tough PVC jacket and is available in white (TL-092463) or black (TL-092887).



PARAMETER	SPECIFICATIONS
Impedance	50 ± 2.0 ohms
Velocity of propagation	80%
Center conductor	Solid copper, 0.037"± 0.001"
Shield #1	Foil, aluminum/poly tape (adhered to dielectric)
Shield #2	Braid, 90% 36-AWG tin/copper
Outer jacket	White or Black PVC, lead-free
Outer jacket rating	UL Type CM
Outer diameter	0.178"± 0.006"
Attenuation dB/100'	12.5 dB @ 900 MHz 23.6 dB @ 2.5 GHz 27.5 dB @ 4.0 GHz 35.0 dB @ 6.0 GHz
Installation temperature	0°C to +65°C
Operating temperature	-20°C to +65°C

TE TECHNICAL SUPPORT CENTER

USA:	+1 (800) 522-6752
Canada:	+1 (905) 475-6222
Mexico:	+52 (0) 55-1106-0800
Latin/S. America:	+54 (0) 11-4733-2200
Germany:	+49 (0) 6251-133-1999
UK:	+44 (0) 800-267666
France:	+33 (0) 1-3420-8686
Netherlands:	+31 (0) 73-6246-999
China:	+86 (0) 400-820-6015

te.com

TE, and TE connectivity (logo) are trademarks owned or licensed by the TE Connectivity Ltd. family of companies. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

TE Connectivity warrants to the original end user customer of its products that its products are free from defects in material and workmanship. Subject to conditions and limitations TE Connectivity will, at its option, either repair or replace any part of its products that prove defective because of improper workmanship or materials. This limited warranty is in force for the useful lifetime of the original end product into which the TE Connectivity product is installed. Useful lifetime of the original end product may vary but is not warranted to exceed one (1) year from the original date of the end product purchase.

©2022 TE Connectivity. All Rights Reserved.

08/22 Original