

DRAWING NO: FAD1565-1690-7-C


THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FAD1565-1690-7 SUITS CONDUCTOR

DEADEND

| STRANDING/CONDUCTOR | COND. TYPE | DIAMETER | FITTING LAY |
|------------------------|------------|-------------|-------------|
| 19/3.25 | AAC/AAAC | 16.25 | RIGHT HAND |
| 19/0.128 | AAC/AAAC | 16.26 | RIGHT HAND |
| COVERED CONDUCTOR XPLE | AAC/AAAC | 15.65-16.90 | RIGHT HAND |



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FAD1565-1690-7
DESCRIPTION: FULL-TENSION ALUMINIUM DEADEND
MATERIAL: ALUMINIUM ALLOY
NUMBER OF RODS: 6
ROD DIAMETER: 4.06mm
OVERAL LENGTH: 1020mm
END FINISH: CHAMFERED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: ORANGE

PRODUCT LABEL

FAD1565-1690-7
 19/3.25 AAC/AAAC
 19/0.128 AAC/AAAC
 XLPE 15.65-16.90

WEIGHT: 0.47kg
BATCH NO:
MONTH/YEAR:

BOX LABEL

P/N: FAD1565-1690-7
ID:
DESCRIPTION:
FULL-TENSION ALUMINIUM DEADEND
 19/3.25 AAC/AAAC
 19/0.128 AAC/AAAC
 XLPE 15.65-16.90
RANGE: 15.65 - 16.90
COLOUR-CODE: ORANGE
QTY: 15 **WEIGHT:** **BATCH:**

| | | | | | | | | | | | | | | | | |
|------|-----|-----------------|-------------|------------|------|-----|---|--|---|--|---------------------------------|---|--|--------------------------------|-------------------|----------|
| LOC | | | | | | | IMPLIED NOTES BURRS AND SHARP EDGES REMOVED SCREW THREADS ARE TO AS 1275 DO NOT WORK TO DIMS MARKED REF SURFACE FINISH 6.3 U.N.O. DIMS ARE IN mm. DO NOT SCALE | IMPLIED TOLERANCES HOLE DIA AND LOCATIONS: ±0.5mm. DIMENSIONS UP TO 30mm: ±1.5mm. DIMENSIONS OVER 30mm: ±5%. UP TO A MAX OF: ±5mm. ANGULAR DIMENSIONS: ±5°. | TCPN - PART Alias UTX/DUL FAD1565-1690-7 Cat No FAD1565-1690-7 | TITLE FULL TENSION ALUMINIUM DEADEND (FAD) FITTING COND. RANGE: Ø15.65-Ø16.90 19/3.25 & 19/0.128 AAC/AAAC XLPE 15.65-16.90 | DRAWN RN CHECKED MN | DATE 15-05-2013 APPROVED AT | TE Connectivity 2/3 Corella Close Berkeley Vale NSW 2261 Australia | | | |
| DIST | — | I | NEW RELEASE | 15-05-2013 | RN | AT | MATERIAL DESC ALUMINIUM ALLOY | MATERIAL NO - | MATL SPEC/STD/DRG NO - | PROCESS SPEC HEAT TREAT/PLATING NO - | SIZE A3 | PROJECTION 3RD ANGLE | SCALE NTS | DRAWING NO FAD1565-1690-7-C | SHEET OF 1 1 | REV 1 |
| POS | REV | REVISION RECORD | | | DATE | DWN | APVD | | | | Format: generic_m03.au_r1.frm 4 | Template: tec_generic_a3_metric.au_r1.drw 3 | Dwg No from P1 Mod Fam Tbl: 2 >AUXXXXX | | | |

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.