



SEE NOTE 3 ↔

SEE NOTE 1 ↔

SEE NOTE 2 ↔

ITEM	PART/DRG NO	QTY	DESCRIPTION
1	01-803-0016	4	ENGRAVING LABEL - WHITE/BLACK/WHITE - 80x35mm
2	01-807-0118	1	SINGLE SIDED FOAM TAPE - 10mm x 2mm x 25m REEL ( FOR APPROX REQUIRED LENGTH, SEE NOTE )
3	01-807-0434	1	4-WAY LINK BOX ENCLOSURE SET - MK2 & MK3 LINKBOX (UR6045TMB)
4	01-807-0442	1	LINK BOX ENCLOSURE 2-PIECE COVER 4-WAY (MK2 & MK3 LINKBOX)
5	BAH-018070592	1	RECYCLED LDPE 4 WAY LINK BOX BASE PAD : 820mm X 670mm X 12mm THICK
6	BAH-018110108	1	4-WAY VAC-FORMED DIVING BELL - MK3 LINK BOX
7	BAH-018110112	1	4-WAY DIVING BELL LOCKING BAR - MK3 LINKBOX
8	BAH-018110113	1	ADJUSTMENT LOCKING COLLAR - MK3 LINKBOX
9	BAH-018110161	2	LIFTING HANDLE FOR MK3 LINKBOX DIVING BELL
10	BAH-018110178	4	PRE-CAST MK3 LINKBOX 3-CORE STRAIGHT JOINT UPPER HOUSING
11	BAH-018110179	4	PRE-CAST MK3 LINKBOX 3-CORE STRAIGHT JOINT LOWER HOUSING
12	BAH-028110184	1	300mm² 4-WAY 3-CORE PRE-CAST LINKBOX BODY BUILD - STANDARD UK VERSION
13	BAH-028110199	1	4-WAY PRE-CAST LINK / ACCESSORY TOOLBOX ASSEMBLY - MK3 LINKBOX



NOTES :

1. ADD 15mm LONG BEAD OF LOCTITE 595 SUPERFIX CLEAR SILICONE (AVANTE PART 9A430) TO LOWER THREADED AREA OF LOCKING BAR PRIOR TO ASSEMBLY WITH LOCKING COLLAR. ONCE ADJUSTED WITH LOCKING BAR FITTED TO ENCLOSURE AND LOCKING COLLAR JUST MAKING CONTACT WITH DIVING BELL, ALLOW SILICONE TO CURE.
2. LIFTING HANDLES ARE TO BE ATTACHED TO DIVING BELL USING SOLVENT CEMENT (AVANTE PART 0A529).
3. SINGLE SIDED FOAM TAPE TO BE APPLIED TO FLANGES OF STRAIGHT JOINT LOWER HOUSING. LENGTH REQUIRED APPROX 5200mm



Material	VARIES
Finish	VARIES
Tolerances (UOS)	N/A
B&H Short Desc	1713/UK

Part Description	- IF IN DOUBT ASK - DO NOT SCALE -	
300mm² 4-WAY 3-CORE PRE-CAST MK3 LINKBOX	- STANDARD UK VERSION	

Design/Drawn	D M EATON	Date	05-Sep-12	Scale (UOS)	1:15	THIRD ANGLE PROJECTION	A3
TCPN	EE8509-000	Part Weight					
Drawing/Part No	BAH-028110185	Drawing Type	CUSTOMER				Rev D