



SHEET 1 OF 1			
EC #	APPRVD.	DATE	REV.
15-017185	TAM	01DEC15	B

SPECIFICATION

63Amp/40°C 50-60Hz
 480VAC Phase to Phase
 277VAC Phase to Neutral/Gnd
 Hipot rating (2sec.):
 Phase to Ground 1850VDC
 Phase to Phase 1450VDC
 Neutral to Ph/Gnd 1450VDC
 Surge: 2500V - 1,2/50µs
 Burst: 3500V

ATTENUATION

Conn. Mode - 88dBµV at 150kHz
 Dif. Mode - 75dBµV at 150kHz



UNLESS SPECIFIED, TOLERANCE TO BE ±0.51 [0.0201].

SHEET SIZE THIRD ANGLE PROJECTION
 THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE OTHER THAN TYCO ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION, HARRISBURG, PENNSYLVANIA USA.

63AYC10B-3.cxd LAYOUT: New Layout 2



PFI FILTER

TE PART NO.: 6609067-3			
SCALE: 1/2	DATE: 01DEC15	DRAWING NUMBER: 63AYC10B	REV. B
DRW. BY: LJD	DRG: TAM		