



REV C DRC23-64PAA

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. A14864	7/11/95	RDR
A	REVISED PER E.O. P15240	3-3-97	RDR
B	REVISED PER E.O. P16452	4/18/00	C. WOODRUFF
C	REVISED PER E.O. P16859	12-28-00	RDR

- 9 RECOMMENDED SCREW: 7-18 [M4 X 1.79] THREAD-FORMING SCREW. TORQUE: 10-15 IN-LB [1.13-1.69 NM].
- 8 FLATNESS BETWEEN BOSSES: .005 [.12] MAX.
- 7 THIS RECEPTACLE MATES WITH DRC26-24SA-\*\*\*\* AND DRC26-40SA-\*\*\*\* PLUG (\*\*\*\*=ALL MODIFICATIONS).
- 6 CONTACT PLATING - MATING SIDE: GOLD; PCB SIDE: TIN.
- 5 MATERIAL - PLASTIC (BLACK); INSERT: STEEL; SEAL: RUBBER.
- 4 RECEPTACLE IS SUPPLIED WITH 2 DUST CAPS (NOT SHOWN).
- 3 FLANGE SEAL (P/N 0513-029-6406) IS SHIPPED WITH RECEPTACLE.
- 2 DIMENSION TOLERANCE: ±.025 [.64]; PANEL CUTOUT: ±.010 [.25].
- 1 DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

- 11 SURFACE FINISH: 32 RMS OR BETTER;  $\square$  .005 [.12].
- 10 RECOMMENDED SCREW: 8-16 [M5 X 2.24] THREAD-FORMING SCREW. TORQUE: 15-20 IN-LB [1.69-2.26 NM].

SIGNATURE & DATE	
DR	J. APOSTOL 3 JAN 2000
CHK	M. ... 12/28/00
PE	D. Meyer 12/28/00
APPD	R. ... 12-28-00
SCALE	NONE WT

RECEPTACLE  
24 #20 SIZE CONTACTS &  
40 #20 SIZE CONTACTS  
KEY ARRANGEMENTS  
-A- & -A-  
DRC SERIES  
ENVELOPE

CP	MATL. CODE
	The Deutch Company DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545
<b>B</b>	<b>DRC23-64PAA</b>
DWG SIZE	CODE 1139 SHEET 1 OF 1