



REV NC DT04-12PB-P030

REVISIONS			
SYM	DESCRIPTION	DATE	APPROVED
NC	NEW RELEASE PER E.O. PI6262	9-29-99	RDR



4. BORDERS SIGNIFY THAT PINS 1,11,12 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR. PINS 2,3,10 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR. PINS 4,8,9 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR. PINS 5,6,7 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR.

3. THIS DT04-12PB-P030 MATES WITH DT06-12SB-\*\*\*\* (\*\*\*\* = ALL MODIFICATIONS). CONSULT FACTORY FOR MODIFICATIONS.

2. DIMENSIONS ARE ±.025[0.63] UNLESS OTHERWISE SPECIFIED.

1. DIMENSIONS ARE IN INCHES [MILLIMETERS].

NOTES:

6. ORIENTATION OF "DEUTSCH" AND "-P030" TO BE OPTIONAL.

5. MAXIMUM CURRENT RATING FOR THE 3 PIN BUSBAR IS 13 AMPS.

SIGNATURE & DATE	
DR	M. GONZALEZ 9/27/99
CHK	SP 8-28-99
PE	M. O. 9/27/99
APPD	R. Reed 9-29-99
SCALE	NONE WT

DT 12 WAY RECEPTACLE  
KEY ARRANGEMENT -B-  
(4) 3 PIN BUSBARS-NICKEL PLATED  
COLOR: BLACK

ENVELOPE

CP	MATL. CODE
<b>The Deutsch Company</b> DEUTSCH I.P.D. 3850 INDUSTRIAL AVE. HEMET, CALIF. 92545	
<b>B DT04-12PB-P030</b>	
DWG SIZE	CODE SHEET   OF
11139	