


E00001135

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	01DEC2020	AS	MF




TCPN	CATALOGUE NUMBER	CONDUCTOR AREA (mm ²)	STRANDING METRIC	DIMENSIONS (mm)					CRIMP DIE
				A	B	D	F	G	
EB0626-000	BS25-12	25	19/1.35	70	12	30	32	7	38-90AL
BM5872-000	BS35-8	35	19/1.53	70	8	29	32	8.5	38-90AL
EB0627-000	BS35-12	35	19/1.53	70	12	30	32	8.5	38-90AL
EB0628-000	BS50-12	50	19/1.78	70	12	30	32	9.5	38-132AL
EB0629-000	BS70-12	70	19/2.14	70	12	30	32	11	38-132AL
EB0630-000	BS95-12	95	37/1.78	110	12	38	60	13	38-173AL, 40-172AL
EB0634-000	BS150-16	150	37/2.25	120	16	48	60	16.5	38-220AL, 40-220AL
EB0635-000	BS185-14.5	185	37/2.25	120	14.5	48	60	18.5	38-220AL, 40-220AL
EB0636-000	BS185-16	185	37/2.25	120	16	48	60	18.5	38-220AL, 40-220AL
EB0637-000	BS185-18	185	37/2.25	120	18	48	60	18.5	38-220AL, 40-220AL
EB0638-000	BS240-16	240	61/2.25	122	16	48	60	21	38-284AL, 40-283AL
CX5973-000	BS300-16	300	61/2.52	122	16	48	60	23.5	38-284AL, 40-283AL
EB0640-000	BS300-18	300	61/2.52	122	18	48	60	23.5	38-284AL, 40-283AL
BM0445-000	BS400-16	400	61/2.85	153	16	65	70	26.5	40-390AL
EF0663-000	BS500-16	500	61/3.20	153	16	65	70	29.5	40-390AL
EB0641-000	BS500-18	500	61/3.20	153	18	65	70	29.5	40-390AL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. SAMAL	01DEC2020												
DIMENSIONS: mm		CHK S. CHAD	01DEC2020												
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. FRATER	01DEC2020												
<table border="0"> <tr> <td>0 PLC</td> <td>±</td> </tr> <tr> <td>1 PLC</td> <td>±</td> </tr> <tr> <td>2 PLC</td> <td>±</td> </tr> <tr> <td>3 PLC</td> <td>±</td> </tr> <tr> <td>4 PLC</td> <td>±</td> </tr> <tr> <td>ANGLES</td> <td>±</td> </tr> </table>		0 PLC	±			1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ANGLES	±
0 PLC	±														
1 PLC	±														
2 PLC	±														
3 PLC	±														
4 PLC	±														
ANGLES	±														
MATERIAL -		FINISH -		PRODUCT SPEC -	APPLICATION SPEC -										
		WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO E00001135	RESTRICTED TO -									
CUSTOMER DRAWING				SCALE NTS	SHEET 1 OF 2	REV A									

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



TCPN	CATALOGUE NUMBER	CONDUCTOR AREA (mm ²)	STRANDING METRIC	DIMENSIONS (mm)					CRIMP DIE
				A	B	D	F	G	
257358-000	BSS25-12	25	19/1.35	85	22	40	40	7	38-90AL
665986-000	BSS35-12	35	19/1.53	85	22	40	40	8.5	38-90AL
300972-000	BSS95-12	95	37/1.78	120	22	40	60	13	38-173AL, 40-172AL
661576-000	BSS185-12	185	37/2.25	120	22	40	60	18.5	38-220AL, 40-220AL
356382-000	BSS300-12	300	61/2.52	120	22	40	60	23.5	38-284AL, 40-283AL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. SAMAL 01DEC2020														
DIMENSIONS: mm		CHK S. CHAD 01DEC2020														
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M. FRATER 01DEC2020	NAME BI-METAL STALK CRIMP LUGS													
<table border="0"> <tr> <td>0 PLC</td> <td>±</td> </tr> <tr> <td>1 PLC</td> <td>±</td> </tr> <tr> <td>2 PLC</td> <td>±</td> </tr> <tr> <td>3 PLC</td> <td>±</td> </tr> <tr> <td>4 PLC</td> <td>±</td> </tr> <tr> <td>ANGLES</td> <td>±</td> </tr> </table>		0 PLC	±	1 PLC	±	2 PLC	±	3 PLC	±	4 PLC	±	ANGLES	±	PRODUCT SPEC -	RESTRICTED TO -	
0 PLC	±															
1 PLC	±															
2 PLC	±															
3 PLC	±															
4 PLC	±															
ANGLES	±															
MATERIAL -		FINISH -	APPLICATION SPEC -	SIZE A3												
		WEIGHT -	CAGE CODE 00779	DRAWING NO E00001135												
CUSTOMER DRAWING			SCALE NTS	SHEET 2 OF 2												
			REV A													