


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL REL PER LC20-0132-20	01DEC2020	RS	BJ



DESCRIPTION	TE Part No. (RPN)	Conductor AWG/MCM	Dimensions in Inch (mm)			Color Code	Die Index No.	No. of Crimp per side
			(øA) (Barrel ID)	(øC) (Barrel OD)	(L) (Total Length)			
TCSL-8-U	EN3750-328	8	0.18 (4.58)	0.28 (7.12)	1.75 (44.45)	Red	49	2
TCSL-6-U	EN3750-329	6	0.20 (5.0)	0.3 (7.62)	2.38 (60.45)	Blue	7	2
TCSL-4-U	EN3750-330	4	0.25 (6.35)	0.34 (8.64)	2.55 (64.77)	Gray	8	2
TCSL-2-U	EN3750-331	2	0.31 (7.87)	0.42 (10.67)	2.82 (71.63)	Brown	9	2
TCSL-1-U	EN3750-627	1	0.36 (9.14)	0.47 (11.94)	3.07 (77.98)	Green	11	2
TCSL-1/0-U	EN3750-332	1/0	0.4 (10.16)	0.52 (13.21)	3.06 (77.72)	Pink	12	2
TCSL-2/0-U	EN3750-333	2/0	0.45 (11.43)	0.57 (14.48)	3.3 (83.82)	Black	13	2
TCSL-3/0-U	EN3750-334	3/0	0.49 (12.45)	0.62 (15.75)	3.3 (83.82)	Orange	14	2
TCSL-4/0-U	EN3750-335	4/0	0.56 (14.22)	0.7 (17.78)	3.57 (90.68)	Purple	15	2
TCSL-250-U	EN3750-336	250	0.6 (15.24)	0.76 (19.3)	3.58 (90.93)	Yellow	16	2
TCSL-300-U	EN3750-337	300	0.65 (16.51)	0.82 (20.83)	4.34 (110.24)	White	17	4
TCSL-350-U	EN3750-338	350	0.7 (17.78)	0.88 (22.35)	4.35 (110.49)	Red	18	4
TCSL-400-U	EN3750-361	400	0.76 (19.3)	0.96 (24.38)	4.62 (117.35)	Blue	19	4
TCSL-500-U	EN3750-339	500	0.83 (21.08)	1.07 (27.18)	4.91 (124.71)	Brown	20	4
TCSL-600-U	EN3750-628	600	0.92 (23.37)	1.19 (30.23)	5.85 (148.59)	Green	22	4
TCSL-750-U	EN3750-362	750	1.03 (26.16)	1.31 (33.27)	6.38 (162.05)	Black	24	4
TCSL-1000-U	EN3750-629	1000	1.17 (29.72)	1.51 (38.35)	6.95 (176.53)	White	27	6

NOTE:
 1. MATERIAL: ETP-COPPER
 2. FINISH: ELECTRO TIN PLATED
 3. FOR COPPER CONDUCTOR ONLY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAVI.S 01DEC2020	TE Connectivity		
		CHK J.OPEL 01DEC2020			
DIMENSIONS: INCHES(mm) 		APVD J.OPEL 01DEC2020	NAME		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC	COPPER COMPRESSION SLICES LONG BARREL		
MATERIAL SEE NOTES		APPLICATION SPEC	SIZE A3	CAGE CODE 00779	DRAWING NO C-E00001662
FINISH SEE NOTES		WEIGHT -	RESTRICTED TO		
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A