



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-017666	28DEC2020	GK	MN

LABEL AND LINER DESIGN





PRESENTATION



DESCRIPTION	TEPN	MATERIAL DESCRIPTION	TTDS	Weight (g)	Roll Diameter (mm) ± 10	Roll Diameter (Inch) ± 0.393
EET-0517P-4	3-1768017-0	YELLOW POLYESTER	TTDS-174	0.010	103.82	4.09
EET-0517P-8A	3-1768017-1	SILVER POLYESTER	TTDS-175	0.008	103.82	4.09
EET-0517P-9	3-1768017-2	WHITE POLYESTER	TTDS-177	0.008	102.05	4.02
EET-0517PY-9	3-1768017-3	WHITE POLYETHYLENE	TTDS-178	0.009	107.76	4.24

**INSIDE WOUND
LABEL ACROSS: 4
PER ROLL QTY: 10000**

ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28DEC2020 GOPALAKRISHNA HV		 TE Connectivity	
LABEL HEIGHT:	± 0.3 [.012]	DIMENSIONS: mm [INCHES]		CHK 28DEC2020 MIKE NUTTAL			
LABEL WIDTH:	± 0.3 [.012]			TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC $\pm -$ 1 PLC $\pm -$ 2 PLC $\pm -$ 3 PLC $\pm -$ 4 PLC $\pm -$ ANGLES $\pm -$		APVD 28DEC2020 MIKE NUTTAL	
WEB WIDTH:	± 0.8 [.031]					PRODUCT SPEC SEE TABLE	
VERTICAL REPEAT:	± 0.8 [.031]*			MATERIAL SEE TABLE		APPLICATION SPEC -	
HORIZONTAL REPEAT:	± 0.8 [.031]*	FINISH -		WEIGHT SEE TABLE		DRAWING NO EET-0517	
PRINT POSITIONING:	± 0.8 [.031]*			CUSTOMER DRAWING		RESTRICTED TO -	
LEFT MARGIN:	± 0.4 [.016]			SCALE NTS		SHEET 1 OF 1	
QUANTITY:	-0 % +2 % *NON ACCUMULATING					REV B	