

4

3

2

1

THIS DRAWING IS UNPUBLISHED DIFFUSION RESTREINTE

RELEASED FOR PUBLICATION LIBRE A LA DIFFUSION

© COPYRIGHT- TE CONNECTIVITY

ALL RIGHTS RESERVED

REVISIONS

REV	DESCRIPTION /MODIFICATIONS	DATE	DWN	APVD
1	NEW DRAWING	26MAR2020		

*UNCOATED VERSIONS AVAILABLE

NOTES

- DIMENSIONS IN mm. a = AS SUPPLIED, b = AFTER FREE RECOVERY
- STANDARD LENGTHS P: 1000 mm, 1200 mm and 1500 mm. OTHER CUT LENGTHS AVAILABLE UNDER REQUEST
- MAXIMUM LONGITUDINAL CHANGE AFTER FREE RECOVERY: +5%/-15%
- STANDARD CUT LENGTH TOLERANCES:
 - ± 6 mm (P ≤ 200)
 - ± 9 mm (P > 200)
 - ± 13 mm (P > 300)
 - ± 15 mm (P > 450)
 - 0/+40 mm (P > 1000)
- STANDARD PRINTING /S (COATED): LOGO, FCSM, PRODUCT SIZE, BATCH NUMBER
STANDARD PRINTING /U (UNCOATED): LOGO, FCSM, PRODUCT SIZE, -U, BATCH NUMBER

PRODUCT SIZE	APPLICATION RANGE (mm)		H		W
	From mm	To mm	a MIN	b MAX	b MIN
FCSM 9/3	3.5	8	9	3	2
FCSM 19/6	6.5	17	19	6	2.4
FCSM 28/9	10	25	28	9	3.2
FCSM 38/12	13	34	38	12	4.1
FCSM 51/16	17.5	46	51	16	4.1
FCSM 68/22	24	61	68	22	4.1
FCSM 90/30	33	81	90	30	4.1
FCSM 120/40	44	108	120	40	4.1
FCSM 177/63	69	159	177	63	4.1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWM

TE Connectivity

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

CHK ANM

APVD ANM

PRODUCT SPEC

NAME

FCSM HEAT SHRINK FLAME RETARDANT TUBING

APPLICATION SPEC

SIZE FORMAT

CAGE CODE

DRAWING NO

RESTRICTED TO

WEIGHT

A3

EPD-202-311924-01

MATERIAL

FINISH

CUSTOMER DRAWING

SCALE NTS

SHEET 1

REV 1