

4

3


2

1

© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	NEW DRAWING	24FEB2020	RK	GS



NOTES:

1. MATERIAL: JACKET – CROSS LINKED POLYOLEFIN BASED; COLOUR: BLACK
2. CONTINUOUS USE TEMP: -40° C TO 85° C
3. MIN RECOVERY TEMP 120° C

Cable cross section mm ²	L: Min. Length mm	L: Max. Length mm
1.5–10	100	500/650/700/1200
4–35	150	500/650/700/1200
25–70	260	500/650/700/1200
50–150	315	500/650/700/1200
150–400	330/370	500/650/700/1200

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA K 24FEB2020		
DIMENSIONS: mm		CHK GREG S 24FEB2020		
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME -
MATERIAL SEE NOTE		FINISH -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT - SCALE NTS
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		DRAWING NO A3 00779 C-EPD-202-312003-01 SHEET 1 of 1 REV 1
		CUSTOMER DRAWING		RESTRICTED TO -