





COIL: @ +25° C	
RESISTANCE	40 OHMS ± 10%
NOMINAL VOLTAGE	6.0 VDC
MUST OPERATE	3.5 VDC
MUST RELEASE	2.0 VDC MAX 35 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's
SHOCK 100 g's 6 ± 1 MS. DURATION
TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE & RELEASE 4 MS MAX
CONTACT STABILIZATION 2 MS MAX

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 7/31/95	CK 7/31/95 MB
------------------	---------------

 COMMUNICATIONS
INSTRUMENTS, INC.

CUST. QPL
CUST. NO. M39016/6-121M

TYPE "HFW" RELAY

HFV1131F01M