



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# KAPTON LABELS OVERVIEW

SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
T1K	A33671-000	T1K-254097-10-9	KP228, Kapton white gloss (0,063 mm), Acrylic adhesive	TTDS-034
T2K	D71498-000	T2K-254097-10-9	KP842, Kapton white gloss (0,118 mm), Acrylic adhesive	TTDS-035

Quantity per roll: 10.000 PCs  
 Labels across: 3  
 Winding: outside  
 length of roll: 42,4 m



KAPTON SERIES

All dimensions in mm [inch]  
 labels are centered on the liner  
 as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity	
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,12]	DIMENSIONS mm [INCHES] TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK S. Iser / 01.04.2020 DATE	Name Kapton Label Size „254097“		SIZE A3 CAGE CODE C2290 DRAWING NO. C-KAPTON RESTRICTED TO	
	ADHESIVE	LABEL WIDTH:	±0,3 [0,12]		APVD S. Iser / 01.04.2020 DATE				
	LINER	WEB WIDTH:	±0,8 [0,31]	MATERIAL SEE TABLE FINISH GLOSS UNPRINTED MATT PRINTED	PRODUCT SPEC DATE	CUSTOMER DRAWING SHEET 1 of 1 REV A1			
		VERTICAL REPEAT:	±0,8 [0,31]*		APPLICATION SPEC DATE				
		HORIZONTAL REPEAT:	±0,8 [0,31]*		WEIGHT T1K: 0,025 g   T2K: 0,037g				
		PRINT POSITIONING:	±0,8 [0,31]*						
		LEFT MARGIN:	±0,4 [0,16]						
		QUANTITY:	-0% +2%						
		*NON ACCUMULATING							