


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - LEB-0619P-4 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	DRAWING FORMAT UPDATE	21DEC2018	GK	KM



LABEL ACROSS: 9
LABELS PER SHEET: 396
LABELS PER PACK: 3960
SHEETS PER PACK: 10


All dimensions in mm [INCHES]

Print Colour	Description	Material	Nom. Thickness	Adhesive Type	Part number
	LEB-0619P-8A	PE200 Silver Polyester	0.05 mm	Acrylic, permanent	1-1768033-1
	LEB-0619P-9	PE201 White Polyester	0.05 mm	Acrylic, permanent	1-1768033-2
	LEB-0619P-8	PE202 Silver-grey Polyester	0.05 mm	Acrylic, permanent	1-1768033-0
	LEB-0619P-4	PE216 Yellow Polyester	0.05 mm	Acrylic, permanent	1768033-9
	LEB-0619PF-4	GW201 Yellow Polyester cloth	0.10 mm	Acrylic, permanent	1-1768033-3

TOLERANCES mm [INCHES]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]



MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ±
 1 PLC ±
 2 PLC ±
 3 PLC ±
 4 PLC ±
 ANGLES ± -

DWN	21DEC2018	GOPALAKRISHNA HV
CHK	21DEC2018	K. MUNZ
APVD	21DEC2018	K. MUNZ
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT	0.04 g	
CUSTOMER DRAWING		

		TE Connectivity	
NAME LEB - POLYESTER LABELS ON SHEET			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	C2290	LEB-0619	-
SCALE	NTS	SHEET	1 of 1
REV	B		