


P	LTR	DESCRIPTION	DATE	DWN	APVD
B		ECR-23-190441	23OCT2023	SL	AK



LABEL ACROSS: 4
LABELS PER SHEET: 88
LABELS PER PACK: 880
SHEETS PER PACK: 10

All dimensions in mm [INCHES]

Print Colour	Description	Material	Nom. Thickness	Adhesive Type	Part number
	LEB-1040P-8A	Silver Polyester	0.05 mm	Acrylic, permanent	6-1768033-7
	LEB-1040P-8	Silver-grey Polyester	0.05 mm	Acrylic, permanent	6-1768033-6
	LEB-1040P-4	Yellow Polyester	0.05 mm	Acrylic, permanent	6-1768033-5

TOLERANCES mm [INCHES]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED	
mm [INCHES]			
	0 PLC	±	
	1 PLC	±	
	2 PLC	±	
	3 PLC	±	
	4 PLC	±	
	ANGLES	±	
MATERIAL	SEE TABLE	FINISH	-

DWN	S. LAZRAC	19OCT2023
CHK	Y. BONINO	19OCT2023
APVD	A. KEAN	19OCT2023
PRODUCT SPEC		
APPLICATION SPEC		
WEIGHT	0.17g	
CUSTOMER DRAWING		

		TE Connectivity	
NAME			
LEB - POLYESTER LABELS ON SHEET			
-			
-			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	A00YM	C=LEB-1040	-
SCALE		SHEET	REV
NTS		1 of 1	B