

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	NEW DRAWING	12JUL2020	KR	BHR



1.) MXAW Joint





2.) MXSB Branch Joint



3.) MXSE Live end seal

Type	Material	L (mm approx.)
MXAW Joint	MXAW-5131	1000mm
	MXAW-5132	1000mm
	MXAW-5141	1100mm
	MXAW-5151	1100mm
	MXAW-5161	1100mm
	MXAW-6131	1100mm
MXSB Branch Joint	MXSB-12A/1XU-2XU	700mm
	MXSB-12B/1XU-2XU	800mm
	MXSB-12C/1XU-2XU	800mm
	MXSB-24A/1XU-2XU	700mm
	MXSB-24B/1XU-2XU	800mm
	MXSB-24C/1XU-2XU	800mm
MXSE Live end seal	MXSE-3131	700mm
	MXSE-3141	800mm
	MXSE-3151	800mm
	MXSE-3161	800mm
	MXSE-5121	700mm
	MXSE-5131	700mm
	MXSE-5141	800mm
	MXSE-5151	800mm
	MXSE-6151	800mm
	MXSE-6151	900mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12JUL2020 RAGHAVENDRA K.	 TE Connectivity	
		CHK 12JUL2020 BHAGATH HR		
		APVD 12JUL2020 BERND GRAEVE	NAME MV H/S Joints	
DIMENSIONS: mm 		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC - APPLICATION SPEC - WEIGHT -
MATERIAL -		FINISH -		SIZE A3 CAGE CODE 00779 DRAWING NO. C=MV_H-S RESTRICTED TO -
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 4 REV 1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



4.) MXST Joint



5.) MXSU Transition Joint



6.) MXSU single Core joint


Type	Material	L (mm approx.)
MXST Joint	MXST-3331	1500mm
	MXST-3332	1500mm
	MXST-5311	1500mm
	MXST-5331	1500mm
	MXST-5332	1700mm
MXSU Transition Joint	MXSU-12A/1XU-3SB	1100mm
	MXSU-12B/1XU-3SB	1100mm
	MXSU-12C/1XU-3SB	1100mm
	MXSU-12D/1XU-3SB	1200mm
	MXSU-12E/1XU-3SB	1200mm
	MXSU-24A/1XU-3SB	1100mm
	MXSU-24B/1XU-3SB	1100mm
	MXSU-24C/1XU-3SB	1200mm
	MXSU-24D/1XU-3SB	1200mm
	MXSU-24E/1XU-3SB	1200mm
MXSU single Core joint	MXSU-3121	600mm
	MXSU-3131	600mm
	MXSU-3141	650mm
	MXSU-3151	650mm
	MXSU-3161	700mm
	MXSU-3171	700mm
	MXSU-3181	700mm
	MXSU-3311	1000mm
	MXSU-3321	1100mm

Type	Material	L (mm approx.)
MXSU single Core joint	MXSU-3331	1150mm
	MXSU-3332	1250mm
	MXSU-4111	600mm
	MXSU-4121	600mm
	MXSU-4131	600mm
	MXSU-4132	600mm
	MXSU-4141	650mm
	MXSU-4311	1000mm
	MXSU-4331	1150mm
	MXSU-4332	1250mm
	MXSU-5121	650mm
	MXSU-5131	650mm
	MXSU-5132	700mm
	MXSU-5151	700mm
	MXSU-5171	700mm
	MXSU-5181	700mm
	MXSU-5311	1150mm
	MXSU-5321	1250mm
	MXSU-5331	1300mm
	MXSU-5332	1350mm
	MXSU-6111	650mm
	MXSU-6121	700mm
	MXSU-6131	700mm
	MXSU-6151	800mm
MXSU-6161	800mm	
MXSU-6171	800mm	
MXSU-6181	800mm	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12JUL2020 RAGHAVENDRA K.	TE Connectivity
		CHK 12JUL2020 BHAGATH HR	
DIMENSIONS: mm		APVD 12JUL2020 BERND GRAEVE	NAME MV H/S Joints
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC -	
MATERIAL -		FINISH -	RESTRICTED TO -
		WEIGHT -	SIZE A3 CAGE CODE 00779 DRAWING NO C=MV_H-S
		CUSTOMER DRAWING	SCALE NTS SHEET 2 of 4 REV 1

© - TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



7.) MXSU Repair Joint



8.) MXSU T-Joint



9.) MXSW Joint

Type	Material	L (mm approx.)
MXSU Repair joint	MXSU-3111-L	900mm
	MXSU-3131-L	900mm
	MXSU-3132-L	900mm
	MXSU-3141-L	900mm
	MXSU-5111-L	900mm
	MXSU-5131-L	900mm
	MXSU-5132-L	900mm
	MXSU-5141-L	900mm
	MXSU-5151-L	900mm
	MXSU-6131-L	1000mm
MXSU T-Joint	MXSU-3131-T2	600mm
	MXSU-3141-T4	650mm
	MXSU-3151-T6	650mm
	MXSU-3161-T6	750mm
	MXSU-3161-T7	750mm
	MXSU-3181-T8	650mm
	MXSU-4131-T2	600mm
	MXSU-5131-T2	650mm
	MXSU-5141-T4	700mm
	MXSU-5151-T6	750mm
	MXSU-5161-T6	750mm
	MXSU-5161-T7	750mm
	MXSU-5171-T8	700mm
	MXSU-5181-T8	700mm
	MXSU-6141-T4	750mm
	MXSU-6151-T6	800mm
	MXSU-6161-T6	800mm
	MXSU-6161-T7	800mm
MXSU-6171-T8	800mm	
MXSU-6181-T8	800mm	
MXSW Joint	MXSW-3331	1400mm
	MXSW-3332	1400mm
	MXSW-4332	1400mm
	MXSW-5331	1550mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -

MATERIAL	FINISH
-	-

DWN	12JUL2020
RAGHAVENDRA K.	
CHK	12JUL2020
BHAGATH HR	
APVD	12JUL2020
BERND GRAEVE	
PRODUCT SPEC	
APPLICATION SPEC	
WEIGHT	
CUSTOMER DRAWING	

TE Connectivity

NAME: MV H/S Joints

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	CV-MV_H-S	-

SCALE: NTS SHEET: 3 of 4 REV: 1

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-



10.) SXAW Joint



11.) SXSU 3 core Joint



12.) SXSU Joint



13.) SXSU single Core Joint

Type	Material	L (mm approx.)
SXAW Joint	SXAW-3131	1000mm
	SXAW-3141	1000mm
	SXAW-3151	1100mm
	SXAW-5131	1000mm
	SXAW-5141	1000mm
	SXAW-5151	1100mm
	SXAW-6132	1100mm
	SXAW-6142	1200mm
SXSU 3 core Joint	SXSU-3121	650mm
	SXSU-3131	700mm
	SXSU-3141	750mm
	SXSU-3321	1400mm
	SXSU-3331	1600mm
	SXSU-4131	700mm
	SXSU-4322	1700mm
	SXSU-5131	700mm
	SXSU-5132	700mm
	SXSU-5322	1700mm
	SXSU-5332	1700mm
	SXSU-6132	800mm
SXSU single core Joint	SXSU-4121	650mm
	SXSU-4141	800mm
	SXSU-4151	750mm
	SXSU-5121	650mm
SXSU Joint	SXSU-5141	800mm
	SXSU-5151	750mm
	SXSU-6122	800mm
	SXSU-6142	900mm
SXSU 3 core Joint	SXSW-4304	1500mm
	SXSW-4314	1500mm
	SXSW-4324	1500mm
	SXSW-4334	1800mm

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12JUL2020 RAGHAVENDRA K.	TE Connectivity	
		CHK 12JUL2020 BHAGATH HR		
		APVD 12JUL2020 BERND GRAEVE	NAME MV H/S Joints	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A3
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		CAGE CODE 00779
MATERIAL -		FINISH -		DRAWING NO G-MV_H-S
		WEIGHT		RESTRICTED TO -
		CUSTOMER DRAWING		SCALE NTS
		SHEET 4 of 4		REV 1