



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-21-110870	27AUG2021	GK	MN

LABEL AND LINER DESIGN



PRESENTATION




All dimensions in mm [Inches]

TE PN: F31612-000

**OUTSIDE WOUND
LABEL ACROSS: 3
PER ROLL QTY: 10000**

MATERIAL	NYLON CLOTH
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES ± — ± — ± — ± — ± — ± —
MATERIAL	FINISH
SEE TABLE	—

DWN	27AUG2021	 TE Connectivity					
GOPALAKRISHNA HV							
CHK	27AUG2021	NAME NC - NYLON CLOTH LABELS - -					
MIKE NUTTALL							
APVD	27AUG2021						
MIKE NUTTALL							
PRODUCT SPEC							
TTDS-051		SIZECAGE CODEDRAWING NORESTRICTED TO A3C2290C-NC-254097-10-9- - -					
APPLICATION SPEC							
-							
WEIGHT	0.059g	-					
CUSTOMER DRAWING		SCALE	NTS	SHEET	1 of 1	REV	B