



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	REVISED PER ECR-20-003865	16MAR2020	RK	HD

Component 1 HTAT-24/6


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5050/A-X



PRODUCT DIMENSIONS & NOTES

DIMENSIONS (in millimetres)

Component 1: HTAT-24/6-0			Component 2: RBK-105-NR5050/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
24.0	6.00	2.25	8.50	6.50	2.75	19.75	1.0
Supplied cut length 45mm ±1.5mm			Supplied cut length 8mm ±0.8mm				
MATERIAL: JACKET: Flame Retarded Modified Polyolefin (Colour: Black) LINER: Hot Melt Adhesive (Colour: Amber)			MATERIAL: Hot Melt Adhesive (Colour: Amber)				

© 2015 TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN	HD	10MAR2015	MATERIAL	-	FINISH	-
	CHK	CD	10MAR2015				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	CD	10MAR2015				
	0 PLC	± -	PRODUCT SPEC	108-120026	NAME	RBK-105-KIT-0105-A0	
1 PLC	± -	APPLICATION SPEC	-	SIZE	A4	CAGE CODE	-
2 PLC	± -	WEIGHT	2.82 g	DRAWING NO	RBK-105-KIT-0105-A0		RESTRICTED TO
3 PLC	± -		CUSTOMER DRAWING	SCALE	NTS	SHEET	1 of 1
4 PLC	± -			REV	A1		
ANGLES	± -						