



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-20-005864	22APR2020	RK	HD

Component 1 HTAT-24/6


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5050/A-X



PRODUCT DIMENSIONS & NOTES

DIMENSIONS (in millimetres)

Component 1: HTAT-24/6-0			Component 2: RBK-105-NR5050/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
24.0	6.00	2.25	8.50	6.50	2.75	19.75	1.0
Supplied cut length 45mm ±1.5mm			Supplied cut length 8mm ±0.8mm				
MATERIAL:			MATERIAL:				
JACKET: Flame Retarded Modified Polyolefin (Colour: Black)			Hot Melt Adhesive (Colour: Amber)				
LINER: Hot Melt Adhesive (Colour: Amber)							

TE Connectivity. All Rights Reserved. © 2015



DIMENSIONS: mm	DWN	16APR2015	MATERIAL	-	FINISH	-
	CHK	16APR2015	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD	16APR2015				
	CD		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
0 PLC ± -	PRODUCT SPEC	108-120026	A4	-	© RBK-105-KIT-0905-A0	-
1 PLC ± -	APPLICATION SPEC	-	WEIGHT	2.82g	CUSTOMER DRAWING	SCALE NTS
2 PLC ± -						SHEET 1 OF 1
3 PLC ± -						REV A1
4 PLC ± -						
ANGLES ± -						

