



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-21-102407	22APR2021	-	HD
	A2	REDRAWN IN CREO	08NOV2023	GDK	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D (D)		MAXIMUM RECOVERED I.D (d)		WALL THICKNESS AFTER RECOVERY (W)	
	mm.	in.	mm.	in.	mm.	in.
1.5/0.5	1.50	0.059	0.50	0.020	0.45±0.10	0.018±0.004
3/1	3.00	0.118	1.00	0.039	0.55±0.10	0.022±0.004
4.5/1.5	4.50	0.177	1.50	0.059	0.55±0.10	0.022±0.004
6/2	6.00	0.236	2.00	0.079	0.65±0.10	0.026±0.004
9/3	9.00	0.354	3.00	0.118	0.75±0.12	0.030±0.005
12/4	12.00	0.472	4.00	0.157	0.75±0.12	0.030±0.005
18/6	18.00	0.709	6.00	0.236	0.85±0.12	0.033±0.005
24/8	24.00	0.945	8.00	0.315	1.00±0.18	0.039±0.007
39/13	39.00	1.535	13.00	0.512	1.15±0.20	0.045±0.008


PRODUCT INFORMATION

1. FLAME RETARDANT
2. MATERIAL: IRRADIATED MODIFIED POLYOLEFIN
STANDARD COLOURS: BLACK, WHITE, RED, BLUE, YELLOW, CLEAR
NON-STANDARD COLOURS: BROWN, ORANGE, GREEN, VIOLET, GREY
3. SHRINK RATIO 3:1
4. LONGITUDINAL CHANGE 0 TO -10%
5. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±0.1
1 PLC ±0.1
2 PLC ±0.01
3 PLC ±0.001
4 PLC ±0.0001
ANGLES ±
FINISH -

DWN	08NOV2023
GAGANA D K	
CHK	08NOV2023
BASAVARAJA D A	
APVD	08NOV2023
VLADIMIR NEMEC	
PRODUCT SPEC	
RW-2053	
APPLICATION SPEC	
114-120022	
WEIGHT	-
CUSTOMER DRAWING	



NAME RNF-3000-IRRADIATED MODIFIED POLYOLEFIN SINGLE WALL HEAT SHRINK TUBING			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-RNF-3000_STANDARD_SIZES	-
SCALE NTS		SHEET 1 OF 1	REV A2