




REVISION			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE OF CD PER ECO-19-013153	9/18/2019	I. MYONG



NOTES:

1. FLEXIBLE, ADHESIVE TAPE BASED ON ELASTOMERIC POLYMERS.
2. TEMPERATURE RANGE: -55°C – $+135^{\circ}\text{C}$
3. TAPE IS SUPPLIED ON 100 FOOT REEL
 $3/4$ " WIDE X $.018$ " THICK X 100FT
4. SPECIFICATIONS:
RT-1050/13
5. SDS DOCUMENTS:
RAY 2010
6. SHELF LIFE:
REFER TO TE SPEC SHEET No. 126-116006.

Raychem Harness & Components **CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS, AND INCH DIMENSIONS ARE IN SHOWN IN (PARENTHESES).		 TE Connectivity					
DECIMALS: .000 ± 0.000 .00 ± 0.00 .0 ± 0.0	ANGLES: ± 0° 00'			TITLE: TE/Raychem FLEXIBLE ELASTOMERIC ADHESIVE TAPE			
TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.		DRAWING NO: S1124					
DRAWN: 31May2019 G.Rositano	APPROVED: 19JUL2019 I.Myong	CAGE CODE 06090	CAD FILE: S1124_cd	SIZE: A	SCALE: 	THIRD ANGLE PROJ. 	SHEET: 1_OF_1