

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	06APR2015	GY	CW
	B	ECR-15-013759	29SEP2015	DW	CW
	C	ECR-21-106515	08JUL2021	SQ	CW

M4 screw, recommended tightening torque 1.2Nm

4 X M3 screw, recommended tightening torque 0.5Nm

NOTES:

1. TECHNICAL CHARACTERISTICS:

INSULATION MATERIAL: PC

RATED VOLTAGE: 500V

RATED CURRENT: 16A

INSULATION RESISTANCE: $\geq 400M\Omega$

RATED IMPULSE VOLTAGE: 6KV

POLLUTION DEGREE: 3

FLAMMABILITY: UL94V-0

MATING CYCLES: 500 CYCLES

OPERATION TEMPERATURE: $-40^{\circ}C \sim +125^{\circ}C$ WIRE RANGE: $0.5mm^2 \sim 2.5mm^2$ (AWG20-AWG14)

CONTACT TYPE: SPRING CLAMP

注释:

1. 技术参数:

绝缘材料: PC

额定电压: 500V

额定电流: 16A

绝缘电阻: $\geq 400M\Omega$

脉冲电压: 6KV

污染等级: 3

阻燃等级: UL94V-0

插拔次数: 500 次

工作温度: $-40^{\circ}C \sim +125^{\circ}C$ 接线范围: $0.5mm^2 \sim 2.5mm^2$ (AWG20-AWG14)

接线类型: 弹片压接

不使用防护外壳时芯件的安装开孔图

Panel cut out for inserts for use without hoods/housings

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL

FINISH

DWN 06APR2015

Gino.Yao

CHK 06APR2015

Chris.Wang

APVD 06APR2015

Xiang.Xu

PRODUCT SPEC

108-137044

APPLICATION SPEC

114-137044

WEIGHT

-

Customer Drawing

NAME

HE-006-MS

SIZE

A3

CAGE CODE

00779

DRAWING NO

T2040063101000

RESTRICTED TO

-

HE-006-MS

T2040063101-000

DESCRIPTION

PART NUMBER

TE Connectivity

SCALE

1:1

SHEET

1 OF 1

REV

C

1470-19 (3/13)