

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	13OCT2016	CH	CW
	AI	ECR-18-004585	26MAR2018	DW	CW
	B	ECR-21-117384	15NOV2021	WQR	CW
	BI	ECR-22-161571	30DEC2022	WQR	CW

SCALE 1:1

SCALE 1:1

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC (GRAY)
RATED VOLTAGE: 250V
RATED CURRENT: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: $0.14mm^2 \sim 2.5mm^2$ (AWG26-AWG14)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER NO. REFER TO DRAWING: T20200X10XX000.)

注释:

- 技术参数:
绝缘材料: PC (GRAY)
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
脉冲电压: 4KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: $0.14mm^2 \sim 2.5mm^2$ (AWG26-AWG14)
接线类型: 冷压接
- 端子需要单独订购.
(订购单号参考图面: T20200X10XX000.)

T2080172101-000

HQ-017-M

HQ-017 MALE INSERT
HQ-017公插PART NUMBER
料号PART DESCRIPTION
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 13OCT2016

CHK CHARLIE.HU

APVD KYLE.ZENG

CHRIS.WANG

PRODUCT SPEC

108-137116

APPLICATION SPEC

114-137116

WEIGHT

-

CUSTOMER DRAWING

NAME
HQ-017-M

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - C-T2080172101000 -

SCALE 3:2 SHEET 1 OF 1 REV BI

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	- ±
FINISH	-

1470-19 (3/13)

TE Connectivity