

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	INITIAL	19SEP2017	YC	CW

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250V
RATED CURRENT: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
WIRE RANGE: 0.14~2.5 mm² (26~14 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X20XX000)

注释:

- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
接线范围: 0.14~2.5 mm² (26~14 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20200X20XX000)

T2111122201-007	HMN-012-F	HMN-012 FEMALE MODULE INSERT HMN-012 模块母插
PART NUMBER 料号	PART DESCRIPTION 描述	
TE TE Connectivity		
NAME HMN-012-F		
SIZE	CAGE CODE	DRAWING NO
A3	00779	T2111122201007
CUSTOMER DRAWING		RESTRICTED TO -
SCALE	SHEET	REV
3:2	1 OF 1	B

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
MATERIAL	FINISH
-	-
-	-

DWN	19SEP2017
YORK CHEN	
CHK	19SEP2017
GINO Y AO	
APVD	19SEP2017
CHRIS WANG	
PRODUCT SPEC	108-137121
APPLICATION SPEC	114-137121
WEIGHT	-

TE TE Connectivity			
NAME HMN-012-F			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	T2111122201007	-
CUSTOMER DRAWING	SCALE	SHEET	REV
	3:2	1 OF 1	B

1470-19 (3/13)