








REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	25MAR2015	DW	CW
	B	ECR-15-018270	08DEC2015	DW	CW
	C	ECR-21-111798	29SEP2021	WQR	CW



- NOTES:
- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 160V
RATED CURRENT: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 2.5KV
POLLUTION DEGREE: 2
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: -40~+125°C
WIRE RANGE: 0.14~2.5 mm² (26~14 AWG)
CONTACT TYPE: CRIMP CONTACT
 - CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X10XX000)

- 注释:
- 技术参数:
绝缘材料: PC
额定电压: 160V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 2.5KV
污染等级: 2
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: -40~+125°C
接线范围: 0.14~2.5 mm² (26~14 AWG)
接线类型: 冷压接
 - 端子需要单独订购.
(订货号参考图面: T20200X10XX000)

HMN-017-M	T2111172101-000
DESCRIPTION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	25MAR2015	TE Connectivity		
		CHK	25MAR2015			
		APVD	25MAR2015			
		PRODUCT SPEC	108-137062			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		
mm				HMN-017-M		
		0 PLC	±-	SIZE		
		1 PLC	±-	CAGE CODE		
		2 PLC	±-	DRAWING NO		
		3 PLC	±-	RESTRICTED TO		
		4 PLC	±-			
		ANGLES	±-			
MATERIAL		FINISH		WEIGHT		
-		-	-	-		
-		-	-	Customer Drawing		