

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# TAMPER-PROOF LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	D91458-000	MV-381191-5-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084
TN	E48361-000	TN-381191-5-8A	PE7021, Polyethylene destructive white matt (0,07 mm), Acrylic adhesive	TTDS-091

Quantity per roll: 5.000 PCs

Labels across: 2

Winding: outside

length of roll: 60,6 m



approx. Ø 136-139 [5.355-5.473]

Ø 76,2 [3,00]

Color-appearance on roll



TN white

MV silver

LABEL BUILD DETAILS	TOLERANCES mm [INCH]	THIS DRAWING IS A CONTROLLED DOCUMENT	DWN S. Iser / 01.04.2020 DATE	TE Connectivity
SUBSTRATE	LABEL HEIGHT: ±0,3 [0,012]	DIMENSIONS mm [INCHES]	CHK S. Iser / 01.04.2020 DATE	Name Tamper-proof Label Size „381191“
ADHESIVE	LABEL WIDTH: ±0,3 [0,012]		APVD S. Iser / 01.04.2020 DATE	
LINER	WEB WIDTH: ±0,8 [0,031]	TOLERANCES UNLESS OTHERWISE SPECIFIED	PRODUCT SPEC DATE	SIZE A3 CAGE CODE C2290 DRAWING NO. C-TAMPER-PROOF RESTRICTED TO
	VERTICAL REPEAT: ±0,8 [0,031]*		APPLICATION SPEC DATE	
	HORIZONTAL REPEAT: ±0,8 [0,031]*	MATERIAL SEE TABLE	WEIGHT MV: 0,073 g   TN: 0,0059 g	CUSTOMER DRAWING SHEET 1 of 1 REV A1
	PRINT POSITIONING: ±0,8 [0,031]*		FINISH	
	LEFT MARGIN: ±0,4 [0,016]			
	QUANTITY: -0% +2%			
	*NON ACCUMULATING			

All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

TAMPER-PROOF SERIES