


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	29.04.2020	SI	SI

Single Marker

Sheet Layout



Pre-printed white area
for manual lettering
via pen

Clear gloss self-laminating
area. Light blue color
only for indication of area



188,50
[7.528]

Final Presentation
Envelope

Quantity per sheet: 9 PCs
Sheets in envelope: 10 SH
Total PCs: 90 PCs

Bestell-Nr.	TKM 50	TKM 75	TKM 150
Stückzahl pro Paket	90	60	30
max. Kabel Ø	8 mm	14 mm	38 mm
Farbe Schriftfeld	farbig/weiss	weiss	weiss
Order-Nr.	TKM 50	TKM 75	TKM 150
Number per pack	90	60	30
max. Cable Ø	8 mm	14 mm	38 mm
Text field colour	coloured/white	white	white
No. d'ordre	TKM 50	TKM 75	TKM 150
Nombre par paquet	90	60	30
max. Cable Ø	8 mm	14 mm	38 mm
Zone de texte	teinté/blanc	blanc	blanc



TE PN: 7-1768048-7

All dimensions in mm [inch]

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		TE Connectivity							
	PRINT	LABEL HEIGHT:	±0,3 [.012]	DIMENSIONS mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	DWN	S. Iser / 29.04.2020	TE connectivity	TE Connectivity				
	SUBSTRATE	LABEL WIDTH:	±0,3 [.012]			CHK	S. Iser / 29.04.2020		DATE				
	ADHESIVE	WEB WIDTH:	±0,8 [.031]			APVD	S. Iser / 29.04.2020		DATE				
	LINER	VERTICAL REPEAT:	±0,8 [.031]*			PRODUCT SPEC			DATE				
		HORIZONTAL REPEAT:	±0,8 [.031]*			APPLICATION SPEC			DATE				
		PRINT POSITIONING:	±0,8 [.031]*	WEIGHT	0,080 g	SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO	
		LEFT MARGIN:	±0,4 [.016]	MATERIAL	FINISH	A3		C2290		C-7-1768048-7			
		QUANTITY:	-0% +2%	SEE TABLE	GLOSS UNPRINTED MATT PRINTED	CUSTOMER DRAWING				SHEET 1 of 1		REV A1	
		*NON ACCUMULATING											