



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	24SEP2020	GK	DB

LABEL AND LINER DESIGN

PRESENTATION




All dimensions in mm [Inches]

TE PN: CT92093001

OUTSIDE WOUND
LABEL ACROSS: 3
PER ROLL QTY: 15000

MATERIAL	WHITE POLYESTER
ADHESIVE TYPE	ACRYLIC PERMANENT
LINER	WHITE GLASSINE

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24SEP2020 GOPALAKRISHNA HV		 TE Connectivity					
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – 1 PLC ± – 2 PLC ± – 3 PLC ± – 4 PLC ± – ANGLES ± –	CHK 24SEP2020 D. BURGAT	APVD 24SEP2020 D. BURGAT					NAME White Polyester Chemical Resistant – 19.1 x 11.4mm [0.75 x 0.45inch] –	
LABEL WIDTH:	±0.3 [.012]			PRODUCT SPEC TTDS–301		APPLICATION SPEC –	SIZE A3	CAGE CODE FB1U7	DRAWING NO C–WPCR–191114–15–9		RESTRICTED TO –
WEB WIDTH:	±2.0 [.079]		MATERIAL SEE TABLE	FINISH –	WEIGHT 0.027g	CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1	REV A
VERTICAL REPEAT:	±0.8 [.031]*										
HORIZONTAL REPEAT:	±0.8 [.031]*										
PRINT POSITIONING:	±0.8 [.031]*										
LEFT MARGIN:	±0.7 [.027]										
QUANTITY:	–0 % +2 %										
*NON ACCUMULATING											