


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	DRAWING FORMAT UPDATE AND MATERIAL RE-DESIGN	29JUL2019	GK	KM

PRESENTATION




**OUTSIDE WOUND
LABEL ACROSS: 3
PER ROLL QTY: 10000.
ROLL LENGTH: 31.67 m**

TE PN: E31574-000

MATERIAL	WHITE VINYL FILM
ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC $\pm .$
	1 PLC $\pm .$
	2 PLC $\pm .$
	3 PLC $\pm .$
	4 PLC $\pm .$
	ANGLES $\pm .$
MATERIAL	FINISH
SEE TABLE	-

DWN GOPALAKRISHNA HV		29JUL2019		TE Connectivity							
CHK K. MUNZ		29JUL2019									
APVD K. MUNZ		29JUL2019									
PRODUCT SPEC TTDS-207		NAME WV - WHITE VINYL LABELS - -									
APPLICATION SPEC -		SIZE		CAGE CODE		DRAWING NO		RESTRICTED TO			
WEIGHT 0.01869 g		A3		C2290		C=WV-254064-10-9		-			
CUSTOMER DRAWING						SCALE NTS		SHEET 1 OF 1		REV A	