HOW TRUCKS RULE THE ROADS. SOON, YOU'LL SEE HYDROGEN POWERED ELECTRIC TRUCKS SHARING IT. HERE'S HOW THEY COMPARE

TRADITIONAL	VS	HYDROGEN POWERED FULLY ELECTRIC
500HP	HORSEPOWER	1000HP
625MI	RANGE FROM FILL UP	800MI
30MPH	TOP SPEED (6% INCLINE UP HILL)	65мрн
60secs	0–60 ACCELERATION TIME	30SECS
7.5 MPG	MPG MILES PER GALLON	10MPG



