

Cross Reference for SOLISTRAND Products to AMPOWER Products

November 19, 2021

Rev 1.0

EVERY CONNECTION COUNTS



Cross Reference (SOLISTRAND to AMPOWER)

*Both the SOLISTRAND & AMPOWER Products listed are U. L. Listed & CSA Certified

SOLISTRAND Products	AMPOWER Products	
322252	325703 250 MCM (127mm ²) WIRE RANGE: 231 MCM - 275 MCM (117 mm ² - 139 mm ²)	325803 & 325803-1 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)
322253	NOT AVAILABLE	
322254	325705 250 MCM (127mm ²) WIRE RANGE: 231 MCM - 275 MCM (117 mm ² - 139 mm ²)	325805 & 325805-1 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)
322257	325803 & 325803-1 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)	325903 350 MCM (177 mm ²) WIRE RANGE: 325 MCM - 375 MCM (165 mm ² - 190 mm ²)
322259	325805 & 325805-1 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)	325905 & 325905-1 350 MCM (177 mm ²) WIRE RANGE: 325 MCM - 375 MCM (165 mm ² - 190 mm ²)
322262	326003 400 MCM (203 mm ²) WIRE RANGE: 375 MCM - 450 MCM (190 mm ² - 228 mm ²)	
322264	326005 & 326005-2 400 MCM (203 mm ²) WIRE RANGE: 375 MCM - 450 MCM (190 mm ² - 228 mm ²)	
322275	324447 250 MCM (127mm ²) WIRE RANGE: 231 MCM - 275 MCM (117 mm ² - 139 mm ²)	324448 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)

Cross Reference (SOLISTRAND to AMPOWER)

*Both the SOLISTRAND & AMPOWER Products listed are U. L. Listed & CSA Certified

SOLISTRAND Products	AMPOWER Products	
322276	324448 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)	324449 350 MCM (177 mm ²) WIRE RANGE: 325 MCM - 375 MCM (165 mm ² - 190 mm ²)
322277	324450 400 MCM (203 mm ²) WIRE RANGE: 375 MCM - 450 MCM (190 mm ² - 228 mm ²)	
322279	324462 250 MCM (127mm ²) WIRE RANGE: 231 MCM - 275 MCM (117 mm ² - 139 mm ²)	324463 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)
322281	324465 400 MCM (203 mm ²) WIRE RANGE: 375 MCM - 450 MCM (190 mm ² - 228 mm ²)	
322282	324466 500 MCM (253 mm ²) WIRE RANGE: 450 MCM - 550 MCM (228 mm ² - 279 mm ²)	324467 600 MCM (304 mm ²) WIRE RANGE: 550 MCM - 650 MCM (279 mm ² - 329 mm ²)
322428	NOT AVAILABLE	
322764	325805 & 325805-1 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)	325905 & 325905-1 350 MCM (177 mm ²) WIRE RANGE: 325 MCM - 375 MCM (165 mm ² - 190 mm ²)
323050	325707 250 MCM (127mm ²) WIRE RANGE: 231 MCM - 275 MCM (117 mm ² - 139 mm ²)	325807 300 MCM (152 mm ²) WIRE RANGE: 275 MCM - 325 MCM (139 mm ² - 165 mm ²)

**ANY
CONNECTION
CAN CHANGE
THE WORLD**

EVERY CONNECTION COUNTS

