

HEAVY DUTY TRUCK

CHARGING





AMP+ HVA 630• 850V DC, 40A at +140°C



AMP+ HVA 280

- High diversity (2P & 3P, multiple latching options, inline)
- Up to 600V individually shielded wire and 850V multi-core wire
- 40A at +85°C



HVA HD400

- Compact, rugged design offering transmission-level vibration performance (LV-S3)
- 1000 VDC, 60 A (at 80°C), operating temperature of -40°C to +140°C



IPT-HD

- Enhanced shielding design offering engine-level vibration performance
- Operating temperature of -40°C to +125°C
- Flexible assembly with single wiring harness



Charging Inlet

- Available in kits and pigtails
- IP67 rating, 250 VAC (at 32 A), and 1000 VDC (at 200 A)
- Upgraded conductor sizes for fast charging – DC 70 mm² / PE 25 mm² / AC 6 mm²

