



INDUSTRIAL & COMMERCIAL TRANSPORTATION SERIES BRIEF

High Power Connectivity Solution

TE Connectivity's (TE) high-power AMP MCP 9.5 two position connectors are designed for harsh environment wire-to-wire and wire-to-circuit board connections. They are constructed of heavy-duty thermoplastic and withstand severe vibration and mechanical shock. The connectors feature an integrated

Featured:

AMP MCP 9.5 TWO POSITION CONNECTORS

SPECIFICATIONS

Current Rating:
78 amps using 10 mm²

Maximum Voltage:
28 V DC

Operating Temperature:
-30°C to +100°C

Additional Information:

- Product Specification, 108-18809
- Application Specification, 114-18501
- IP 67 and IP 69K rated with backshell



secondary lock that confirms contact alignment and retention. Several mounting options are available, including inline, flange, sealed flange, and PCB mount, making the connectors suitable for numerous application types. No tools are required for mounting and the connectors feature a slide lock for easy mating. For harsh environment applications that require a high-power, environmentally sealed two position electrical connector, the AMP MCP 9.5 two position connectors are a reliable solution.

Common Part Numbers

Here are some of the common part numbers for AMP 9.5 two position connectors and related products. Several additional products may be available.



Description

Part Number

Receptacle housing, AMP MCP, 2-way, black	1355328-1
---	-----------



Tab housing, AMP MCP, 2 way, black, no flange seal	1394026-2
--	-----------

Tab housing, AMP MCP, 2 way, black, with flange seal	1394026-1
--	-----------



Header, AMP MCP, 2 way, black 180° molded silver pins, PCB mount	2282162-1
--	-----------



Receptacle contact, strip form, size 9.5, 6.0-10.0 mm ² wire, 4.6-6.4 mm insulation, pre-tin plated	1-967590-1
--	------------

Tab contact, strip form, size 9.5, 6.0-10.0 mm ² wire, 4.6-6.6 mm insulation, pre-tin plated	963774-1
---	----------



Wire seal, AMP MCP, 5.8-6.6 insulation, blue	1355437-2
--	-----------

Backshell, AMP MCP, 2 way, 90°, tab and receptacle housing, NW17 tubing	2286685-1
---	-----------



Tool, extraction, 9.5, receptacles	539971-1
------------------------------------	----------

Tool, extraction, 9.5, tabs	1-1579007-7
-----------------------------	-------------

te.com/ict

DEUTSCH, TE Connectivity, and TE connectivity (logo) are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

The information given herein, including drawings, illustrations and schematics which are intended for illustration purposes only, is believed to be reliable. However, TE Connectivity makes no warranties as to its accuracy or completeness and disclaims any liability in connection with its use. TE Connectivity's obligations shall only be as set forth in TE Connectivity's Standard Terms and Conditions of Sale for this product and in no case will TE Connectivity be liable for any incidental, indirect or consequential damages arising out of the sale, resale, use or misuse of the product. Users of TE Connectivity products should make their own evaluation to determine the suitability of each such product for the specific application.

© 2018 TE Connectivity Ltd. family of companies All Rights Reserved.

TS-ICT-AMPMCPA4 06/18 Revision

SERIES BRIEF

Contact us

Ampèrestrasse 12-14
64625 Bensheim Germany

Tel: +49 (0)6251 133-0

www.te.com

TE Connectivity Germany GmbH