



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

TE Part # 3-215308-0
2X30P HV100 REC CON. TE, 7.0MM, TIN


TE Part # 3-215309-0
2X30P HV100 REC CON. TE, 8.5MM

TE Part # 1-215307-5
2X15P HV100 REC CON. TE, 7.0MM


TE Part # 1-829264-5
2X15P HV100 REC.CON.B/TE,6.2MM, NO KINK




TE Part # 1-215309-5
2X15P HV100 REC CON. TE, 8.5MM




TE Part # 3-829410-0
2X30P HV100 REC CON. TE, 6.2MM, TIN




TE Part # 6-534236-5
30 MODII VRT DR CE 100/120



TE Part # 3-829576-0
2X30P HV100 REC CON.B/TE,6.2,SN, NO KINK



TE Part # 2-534236-5
50 MODII VRT DR CE 100/120



TE Part # 1-534236-5
30 MODII VRT DR CE 100/120



TE Part # 3-215307-0
2X30P HV100 REC CON. TE, 7.0MM

Customers Also Bought



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT




TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #206070-8
CABLE CLAMP KIT #17



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM, CONNECTOR HOUSING

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-826656-5_U.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-826656-5_U.3d_igs.zip

English



Customer View Model

[ENG_CVM_CVM_1-826656-5_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

[UL Report](#)

English