

All Signal Header (240)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 185875-1
26POS MQS REC




TE Part # 185903-2
26W MQS HSG RIGHT ANGLE


Customers Also Bought




TE Part #CAT-SIGH262
Signal Header




TE Part #CAT-M8793-CH8172
MQS, CONNECTOR HOUSING




TE Part #1379662-1
12W PLUG HSG ASSY BLACK



TE Part #1418762-1
MCON 1.2 LL TAB STC SN



TE Part #3-1462039-1
IM26GR=IM RELAY 50mW 12V



TE Part #3-2176331-9
CRGP 2512 15K 1%

Document

Product Drawings

26pos MQS .63 header 90deg

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_185904-2_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_185904-2_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_185904-2_O.3d_stp.zip



English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English